


MMK27.5106K100F12L4BULK

Aliases (F601FG106K100CVBLK, MMK27,5106K100F12L4BULK)

Not for New Design • Recommended Replacement Series R60

MMK/F601, Film, Metallized Polyester, General Purpose, 10 uF, 10%, 100 VDC, 85°C, 27.5mm



Click [here](#) for the 3D model.

Dimensions	
L	31.5mm MAX
H	22.5mm MAX
T	11.5mm MAX
S	27.5mm +/-0.4mm
LL	4mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging	Bulk, Bag

General Information	
Series	MMK/F601
Dielectric	Metallized Polyester
Style	Radial
Features	DC Multipurpose Applications
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Notes	Not for new design – the replacement series is: R60.

Specifications	
Capacitance	10 uF
Capacitance Tolerance	10%
Voltage AC	63 VAC
Voltage DC	100 VDC, 77.5 VDC (100C)
Temperature Range	-55/+100°C
Rated Temperature	85°C
Insulation Resistance	500 MOhms
Max dV/dt	3 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.