



Click [here](#) for the 3D model.

General Information

Series	AFCC 190
Style	Feed-Through Capacitor
Description	Small Signal Feed-Through Capacitors
Features	Military, Industrial, Medical, Telecom
RoHS	Yes
Lead	Wire Leads
Terminal Type	Wire

Dimensions

D	19mm MIN
Lead	Wire Leads
A	14mm MIN
B	18mm MIN
D1	Threaded Studs M6
C	65mm MIN

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

Specifications

Voltage DC	400 VDC
Rated Current	30 A
Ripple Current	30 A
Rated Temperature	40°C
Temperature Range	-25/+85°C
Climate Category	25/085/21
Capacitance	0.22 uF

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.