



Click [here](#) for the 3D model.

General Information

Series	AFPI 160
Style	Feed-Through Filter
Description	Small Signal Feed-Through Filters
Features	Military, Industrial, Medical, Telecom
RoHS	Yes
Qualifications	UL
AEC-Q200	No
Lead	Wire Leads
Terminal Type	Wire

Dimensions

D	16mm MIN
Lead	Wire Leads
A	16mm MIN
B	34mm MIN
D1	1.2

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

Specifications

Voltage AC	250 VAC
Voltage DC	600 VDC
Rated Current	16 A
Ripple Current	16 A
Rated Temperature	40°C
Temperature Range	-25/+85°C
Climate Category	25/085/21

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.