



Click [here](#) for the 3D model.

#### General Information

Style	Metal Sealed
Description	Metal Sealed Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
SCIP Number	e8b63861-aef3-4ef5-83bb-6273ea2dbdde
Notes	Female thread type, V Groove.
REACH	SVHC (PZT - CAS 12626-81-2)

#### Specifications

Series	ASL
Displacement	77um +/-12um
Voltage DC	150 VDC
Capacitance	5.1 uF
Tolerance	20%
Resonant Frequency	8 kHz
Generated Force	800 N
Insulation Resistance	5 MOhms
Temperature Range	-40/+150°C

#### Dimensions

D	19.6mm +/-0.5mm
L	98.4mm +/-0.5mm
LL	130mm +/-10mm

#### Packaging Specifications

Typical Component Weight	61
Packaging	Tray
Packaging Quantity	1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.