



Click [here](#) for the 3D model.

Dimensions

D	45mm +1mm
L	71.5mm +/-2mm

Packaging Specifications

Terminal Type	Through-Hole
Terminal Type	Bolt-M8x41
Packaging	Bulk, Bag
Packaging Quantity	50

General Information

Series	C27
Dielectric	Film/Foil Polypropylene
Style	Can
Description	Plastic Case and Cover, Ultra Sonically Welded Seal
Features	Ultra Sonically Welded Seal, Safety Class P0, UL_94 V0 Disk
RoHS	Yes
Termination	Tin Copper
Lead	BiPolar Cables
Qualifications	UL, VDE, UL (Construction Only), UL_94 V0 Disk
AEC-Q200	No
Typical Component Weight	120.5 g

Specifications

Capacitance	20 uF
Capacitance Tolerance	5%
Voltage AC	470 VAC
Temperature Range	-25/+85°C
Rated Temperature	85°C
Max dV/dt	20 V/us