
C277LC24500AA0J

C27, Film, Film/Foil Polypropylene, Motor Run, 5 uF, 5%, 425 VAC





Click	here	for	the	3D	model.

Dimensions				
D	25mm +1mm			
L	56.5mm +/-2mm			
Packaging Specifications				
Packaging Specifications				
Packaging Specifications Terminal Type	Bolt - M8x10			

General Information	
Series	C27
Dielectric	Film/Foil Polypropylene
Style	Can
Description	Plastic Case and Cover, Ultra Sonically Welded Seal
Features	Ultra Sonically Welded Seal, Safety Class PO, UL_94 VO Disk
RoHS	Yes
Lead	Fast On (1+1)
Qualifications	UL, VDE, UL (Construction Only), UL_94 V0 Disk
AEC-Q200	No
Typical Component Weight	26 g

Specifications	
Capacitance	5 uF
Tolerance	5%
Voltage AC	425 VAC
Temperature Range	-25/+85°C
Rated Temperature	85°C
Max dV/dt	15 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO