
CGP7C222MKVDCA7317

CGP DISC Comm HV, Ceramic, 2,200 pF, 20%, 6,000 VDC, Y5V, 7.5 mm





General Information				
Series	CGP DISC Comm HV			
Style	Radial Disc			
RoHS	Yes			
Termination	Tin			
Lead	Crimped Out			
Failure Rate	N/A			
AEC-Q200	No			
Halogen Free	Yes			

CI	ic	k	here	• foi	r the	3D	mod	lel

Dimensions	
D	11mm MAX
Т	8mm MAX
S	7.5mm NOM
LL	16mm +2/-0mm
F	0.6mm +/-0.1mm
V	2.7mm +/-0.5mm

Packaging Specifications		
Packaging	Ammo	
Packaging Quantity	1000	

Specifications	
Capacitance	2,200 pF
Tolerance	20%
Voltage DC	6000 VDC
Temperature Range	-30/+85°C
Temp. Coefficient	Y5V

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/16/2025 © 2006 - 2025 YAGEO