



#### General Information

|                |  |
|----------------|--|
| Series         | EFA  |
| Style          | Sheet  |
| Description    | Flex Suppressor Flame Retardant Type                                   |
| Features       | Flame Retardant Type   |
| RoHS           | Yes  |
| Qualifications | UL94 V-0, UL File No. E176124  |
| Environment    | RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

#### Specifications

|                      |                |
|----------------------|----------------|
| Temperature Range    | -40/+105°C     |
| Permeability         | 60 u At 3MHz   |
| Effective Frequency  | 1 MHz to 3GHz  |
| Specific Gravity     | 3.1 TYP        |
| Thermal Conductivity | 1.27 typical   |
| Surface Resistivity  | 1 MOhm/sq. TYP |

#### Dimensions

|            |             |
|------------|-------------|
| Sheet Size | 240x10mm    |
| L          | 10000mm NOM |
| W          | 240mm NOM   |
| T          | 0.05mm NOM  |

#### Packaging Specifications

|                          |       |
|--------------------------|-------|
| Typical Component Weight | 403 g |
|--------------------------|-------|