



#### General Information

Series	EFA
Style	Sheet
Description	Flex Suppressor Flame Retardant Type
Features	Flame Retardant Type
RoHS	Yes
Qualifications	UL94 V-0, UL File No. E176124
AEC-Q200	No
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

#### Dimensions

Sheet Size	240mmx20M
L	20000mm NOM
W	240mm NOM
T	0.3mm NOM

#### Specifications

Temperature Range	-40 / +105°C
Permeability	60 u At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.1 TYP
Thermal Conductivity	1.27 typical
Surface Resistivity	1 MOhm/sq. TYP

#### Packaging Specifications

Tape Description	Without PET Tape (TxXOO)
Adhesive Thickness	0.03 mm
Typical Component Weight	4,536.96 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.