



| General Information | |
|---------------------|---|
| Series | EFF4 |
| Style | Sheet |
| Description | Flex Suppressor Flame Retardant Type |
| Features | Flame Retardant Type |
| RoHS | Yes |
| Qualifications | UL94 V-0, UL File No.E176124, AEC-Q200 |
| Environment | RoHS Compliant, Halogen Free, PVC Free, Lead Free |

| Specifications | |
|----------------------|----------------|
| Temperature Range | -40/+125°C |
| Permeability | 140 u At 3MHz |
| Effective Frequency | 1 MHz to 3GHz |
| Specific Gravity | 3.7 TYP |
| Thermal Conductivity | 1.52 typical |
| Surface Resistivity | 1 MOhm/sq. TYP |

| Dimensions | |
|------------|-----------|
| Sheet Size | 240x240mm |
| L | 240mm NOM |
| W | 240mm NOM |
| T | 0.1mm NOM |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Tape Description | Without PET Tape (Txx00) |
| Tape Thickness | 0.03mm |
| Typical Component Weight | 23.66 g |