



## General Information

Series	EFF4
Style	Sheet
Description	Flex Suppressor Flame Retardant Type
Features	Flame Retardant Type
RoHS	Yes
Qualifications	UL94 V-0, UL File No.E176124, AEC-Q200
AEC-Q200	Yes
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free

## Dimensions

Sheet Size	240x240mm
L	240mm NOM
W	240mm NOM
T	0.5mm NOM

## Packaging Specifications

Tape Description	No Adhesive Tape
Typical Component Weight	106.56 g

## Specifications

Temperature Range	-40/+125°C
Permeability	140 u At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.7 TYP
Thermal Conductivity	1.52 typical
Surface Resistivity	1 MOhm/sq. TYP

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.