



#### General Information

|                |  |
|----------------|--|
| Series         | EFG3   |
| Style          | Sheet  |
| Description    | Flex Suppressor Flame Retardant Type                                   |
| Features       | Flame Retardant Type   |
| RoHS           | Yes  |
| Qualifications | UL94 HB, UL File No. E176124   |
| Environment    | RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

#### Specifications

|                      |                |
|----------------------|----------------|
| Temperature Range    | -40/+105°C     |
| Permeability         | 42 u At 3MHz   |
| Effective Frequency  | 1 GHz to 10GHz |
| Specific Gravity     | 4.1 TYP        |
| Thermal Conductivity | 1.43 typical   |
| Surface Resistivity  | 1 MOhm/sq. TYP |

#### Dimensions

|            |           |
|------------|-----------|
| Sheet Size | 120x120mm |
| L          | 120mm NOM |
| W          | 120mm NOM |
| T          | 0.2mm NOM |

#### Packaging Specifications

|                          |         |
|--------------------------|---------|
| Tape Thickness           | 0.03mm  |
| Typical Component Weight | 13.65 g |