



#### General Information

|                |  |
|----------------|--|
| Series         | EFW  |
| Style          | Sheet  |
| Description    | Flex Suppressor High Permeability Type                                 |
| Features       | High Permeability Type   |
| RoHS           | Yes  |
| Qualifications | UL94 HB, UL File No. E176124   |
| Environment    | RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

#### Specifications

|                      |                |
|----------------------|----------------|
| Temperature Range    | -40/+105°C     |
| Permeability         | 230 u at 3 MHz |
| Effective Frequency  | 1 MHz to 3GHz  |
| Specific Gravity     | 4 TYP          |
| Thermal Conductivity | 1.27 typical   |
| Surface Resistivity  | 1 MOhm/sq. TYP |

#### Dimensions

|            |           |
|------------|-----------|
| Sheet Size | 80x80mm   |
| L          | 80mm NOM  |
| W          | 80mm NOM  |
| T          | 0.3mm NOM |

#### Packaging Specifications

|                          |        |
|--------------------------|--------|
| Tape Thickness           | 0.03mm |
| Typical Component Weight | 8.24 g |