



Click [here](#) for the 3D model.

### Dimensions

L	37mm +/-1mm
T	12.7mm +/-1mm
H	10mm +/-2mm
A	25.4mm +/-1mm
B	2.6mm +/-1mm

### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	800
Typical Component Weight	23.84 g

### General Information

Series	ESD-FPD-1
Style	Flat - Split
Cable Type	Flat Cable
Description	EMI Core Split, For Flat Cables With Plastic Clamp
Features	Nylon Clamp
RoHS	Yes
Applicable Cable	16 Core
Materials	Ni-Zn

### Specifications

Temperature Range	-25/+85°C
Effective Frequency	500 MHz (FM Band Range)