



Click [here](#) for the 3D model.

#### General Information

Series	ESD-R
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores, Coated Type
RoHS	Yes
Qualifications	UL94 V-2
AEC-Q200	No
Case Color	Green
Materials	Mn-Zn
Core	Mn-Zn Ferrite

#### Specifications

Temperature Range	-25/+85°C
Effective Frequency	10 MHz (AM Band Range)

#### Dimensions

D	15mm MAX
D2	6.2mm MIN
T	3.5mm MAX

#### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	6000
Typical Component Weight	1.8 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.