



Click [here](#) for the 3D model.

General Information

Series	FLLCC
Style	Feed-Through Capacitor
Description	Power Feed-Through Capacitors
Features	Industrial, Medical
RoHS	Yes
Qualifications	UL
AEC-Q200	No

Dimensions

D	25.4mm MIN
B	46mm MIN
D1	Threaded Studs M5
C	57mm MIN

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

Specifications

Voltage DC	100 VDC
Rated Current	25 A
Ripple Current	25 A
Rated Temperature	40°C
Temperature Range	-40/+85°C
Climate Category	40/085/56
Capacitance	0.5 μ F

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.