



Click [here](#) for the 3D model.

## General Information

Series	FLLD3-AW
Style	Chassis Mount
Description	Compact, Three-Phase and Neutral Filters
Features	Three Phase, Compact
Phase	Three-phase
RoHS	Yes
Qualifications	UL 1283
AEC-Q200	No
Lead	Fast On
Terminal Type	Faston

## Dimensions

L	93mm MAX
W	52mm NOM
H	39.5mm NOM
L1	85mm NOM
L2	75mm NOM
Lead	Fast On

## Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

## Specifications

Voltage AC	440 VAC
Rated Frequency	50-60 Hz
Rated Current	10 A
Ripple Current	10 A
Temperature Range	-25/+85°C
Climate Category	25/085/21
Test Voltage DC (P to P)	1700 VDC
Test Voltage DC (P to E)	3000 VDC
Leakage Current	0.018 mA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.