



Click [here](#) for the 3D model.

### Dimensions

A	57.5mm MIN
B	140mm MIN
D1	Threaded Studs M6

### Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

### General Information

Series	FLLDH
Style	Feed-Through Filter
Description	Power Feed-Through Filters
Features	Industrial, Medical
RoHS	Yes

### Specifications

Voltage AC	250 VAC
Voltage DC	440 VDC
Rated Frequency	50-60 Hz
Rated Current	16 A
Rated Temperature	40°C
Temperature Range	-40/+85°C
Climate Category	40/085/56