



Click [here](#) for the 3D model.

General Information

| | |
|----------------|------------------------------------|
| Series | FLLE2-AN |
| Style | Chassis Mount |
| Description | Single Phase Chassis Mount Filters |
| Features | Single Phase |
| Phase | Single-phase |
| RoHS | Yes |
| Qualifications | IEC/EN/UL 60939 |
| AEC-Q200 | No |
| Lead | Threaded Studs M6 |
| Terminal Type | Threaded Studs M6 |

Dimensions

| | |
|-----------|-------------------|
| L | 99mm MIN |
| W | 85mm MIN |
| H | 57mm MIN |
| L1 | 51mm MIN |
| W1 | 95mm MIN |
| W2 | 105mm MIN |
| K | 4.5mm MIN |
| M (Earth) | Threaded Studs M6 |
| Lead | Threaded Studs M6 |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Bulk |
| Packaging Quantity | 1 |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 300 VAC |
| Voltage DC | 480 VDC |
| Rated Frequency | 50-60 Hz |
| Rated Current | 8 A |
| Ripple Current | 8 A |
| Rated Temperature | 40°C |
| Temperature Range | -25/+100°C |
| Climate Category | 25/100/21 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.