


## FLLE2016ARDB

Aliases (LLE2016ARDB)

EMI Filters, KEMET, FLLE2-R, Chassis Mount, Noise Suppression, 600 uH, 65x50x40mm



General Information	
Series	FLLE2-R
Style	Chassis Mount
Description	Single Phase, Chassis Mount Filters
Features	Single Phase
Phase	Single-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL, CSA
AEC-Q200	No
Lead	Fast On
Terminal Type	Faston
Test Voltage DC (P to N)	1300 VDC

Dimensions	
L	65mm MIN
W	50mm MIN
Н	40mm MIN
Lead	Fast On

Specifications	
Voltage AC	300 VAC
Voltage DC	300 VDC
Inductance	0.6 mH
Rated Frequency	50-60 Hz
Rated Current	16 A
Ripple Current	16 A
Rated Temperature	40°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Leakage Current	0.37 mA

2250 VDC

Test Voltage DC (P/N to E)

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	200 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/20/2025 © 2006 - 2025 YAGEO