



Click [here](#) for the 3D model.

Dimensions

| | |
|---|-------------|
| L | 130.5mm MIN |
| W | 56.5mm MIN |
| H | 48.5mm MIN |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Bulk |
| Packaging Quantity | 1 |
| Typical Component Weight | 800 g |

General Information

| | |
|----------------|-------------------------------------|
| Series | FLLE2-U |
| Style | Chassis Mount |
| Description | Single Phase, Chassis Mount Filters |
| Features | Single Phase, Medical |
| Phase | Single-phase |
| RoHS | Yes |
| Qualifications | IEC/EN 60939, UL, CSA |
| Terminal Type | Wire |

Specifications

| | |
|----------------------------|---------------|
| Voltage AC | 300 VAC |
| Voltage DC | 300 VDC |
| Rated Frequency | 50-60 Hz |
| Rated Current | 25 A |
| Rated Temperature | 40°C |
| Temperature Range | -25/+100°C |
| Climate Category | 25/100/21 |
| Leakage Current | 0.86 mA (MAX) |
| Test Voltage DC (P/N to E) | 2250 VDC |
| Test Voltage DC (P to N) | 1300 VDC |