



Click [here](#) for the 3D model.

#### General Information

Series	FLLE2-AN
Style	Chassis Mount
Description	Single Phase Chassis Mount Filters
Features	Single Phase
Phase	Single-phase
RoHS	Yes
Qualifications	IEC/EN/UL 60939
AEC-Q200	No
Lead	Threaded Studs M6
Terminal Type	Threaded Studs M6

#### Dimensions

L	180mm MIN
W	85mm MIN
H	60mm MIN
L1	115mm MIN
W1	100mm MIN
W2	115mm MIN
K	6.5mm MIN
M (Earth)	Threaded Studs M6
Lead	Threaded Studs M6

#### Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

#### Specifications

Voltage AC	300 VAC
Voltage DC	480 VDC
Rated Frequency	50-60 Hz
Rated Current	55 A
Ripple Current	55 A
Rated Temperature	40°C
Temperature Range	-25/+100°C
Climate Category	25/100/21

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.