



#### General Information

Series	FW5
Description	Flex Suppressor High Permeability Type
Features	High Permeability Type
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

#### Specifications

Temperature Range	-40/+105°C
Permeability	250 $\mu$ At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.6 TYP
Thermal Conductivity	1.55 typical
Surface Resistivity	1 MOhm/sq. TYP

#### Dimensions

Sheet Size	240x80mm
L	240mm NOM
W	80mm NOM
T	0.075mm NOM

#### Packaging Specifications

Tape Thickness	0.01mm
Typical Component Weight	7.93 g