



Click [here](#) for the 3D model.

General Information

Series	FYH
Style	Radial Pin
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	Pin Leads
AEC-Q200	No
Typical Component Weight	1.5 g
Miscellaneous	DischargeValue = 0.033 F.

Dimensions

D	11.5mm +/-0.5mm
L	7mm MAX
S	5.08mm +/-0.5mm
LL Negative	3mm MIN
LL Positive	2.7mm MIN
LT1	0.4mm +/-0.1mm
LT2	1.2mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	1600

Specifications

Capacitance	0.022 F
Tolerance	-20/+80%
Voltage DC	5.5 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
ESR	200000 mOhms (1kHz)
Current (at 30 minutes after charging)	0.033 mAmps