



Click [here](#) for the 3D model.

Dimensions	
L	70mm NOM
W	53mm
H	29mm

Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	10
Typical Component Weight	150 g

General Information	
Series	GF
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
SCIP Number	d9c7b340-5c0a-4e16-b4ef-391381f88890
Qualifications	UL
Notes	Last time buy due: May 31, 2024.
Miscellaneous	30 K Self-Temperature Rise Max.
Terminal Type	Screw

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1Min. Line to Ground
Rated Current	20 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-20/+60°C
Leakage Current	1mA MAX (250 V 60 Hz)
ESR	300 MOhms MIN Insulation 500 VDC 1Min. Line To Ground