



Click [here](#) for the 3D model.

General Information	
Series	GT
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
SCIP Number	97462fd0-8e28-4245-8658-d38f8b19fa1l
Qualifications	UL, CSA, TUV
AEC-Q200	No
Miscellaneous	35 K Self-Temperature Rise Max.

Dimensions	
L	84mm NOM
W	50.8mm NOM
H	39mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	10
Typical Component Weight	280 g

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	10 A (AC/DC)
Ripple Current	10 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	0.5 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.