


HT06AB224JN

Obsolete

HP LDD Indust X7R HT200C, Ceramic, 0.22 uF, 5%, 25 VDC, X7R, Commercial, High Temperature, 5.08 mm



General Information	
Series	HP LDD Indust X7R HT200C
Style	Radial
Description	Commercial, High Temperature
Features	LDD High Temperature 200C
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
Termination	Nickel
Lead	Wire Leads
AEC-Q200	No

7.62mm MAX
7.62mm MAX
3.81mm MAX
5.08mm +/-0.762mm
3.175mm MIN
0.635mm +0.102/-0.051mm

Packaging Specifications	
Packaging	Waffle, Tray

Specifications	
Capacitance	0.22 uF
Tolerance	5%
Voltage DC	25 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	X7R

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/23/2025 © 2006 - 2025 YAGEO