




Obsolete

KHA, Ceramic, 1,000 pF, 10%, 1,000 VDC, X7R, 5 mm



YAGEO & KEMET

General Information	
Series	KHA
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No

7.5mm MAX
4.5mm MAX
5mm NOM
0.6mm +/-0.1mm

Packaging Specifications	
Packaging	Ammo, 340x250x50mm Box, H0 = 16mm, Component Pitch = 12.7mm
Packaging Quantity	1000

Specifications		
Capacitance	1,000 pF	
Tolerance	10%	
Voltage DC	1000 VDC	
Temperature Range	-55/+125°C	
Temp. Coefficient	X7R	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/22/2025 © 2006 - 2025 YAGEO