



#### General Information

Series	KHA
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No

#### Dimensions

D	7.5mm MAX
T	4.5mm MAX
S	5mm NOM
F	0.6mm +/-0.1mm

#### Packaging Specifications

Packaging	Ammo, 340x250x50mm Box, H0 = 16mm, Component Pitch = 12.7mm
Packaging Quantity	1000

#### Specifications

Capacitance	1,000 pF
Tolerance	10%
Voltage DC	1000 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R