



Click [here](#) for the 3D model.

General Information

Series	KHB DISC Comm Y5P HV
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No

Dimensions

D	19.5mm MAX
T	4.5mm MAX
S	7.5mm NOM
LL	25mm +/-1mm
F	0.6mm +/-0.1mm

Specifications

Capacitance	6,800 pF
Tolerance	10%
Voltage DC	2000 VDC
Temperature Range	-30/+85°C
Temp. Coefficient	Y5P

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------