



General Information

Style	Bolt-On
Description	Langevin Bolt-On Transducers
RoHS	With Exemptions
Notes	Horn construction; output surface has step or horn shape.
REACH	SVHC (PZT – CAS 12626-81-2)

Dimensions

D	45mm NOM
L	79.5mm NOM

Packaging Specifications

Packaging	Bulk Tray, Box
-----------	----------------

Specifications

Series	NBL
Capacitance	4,000 pF
Resonant Frequency	28 kHz
Dynamic Admittance	40 mS
Mechanical Q	500
Allowable Velocity	40 cm/S
Allowable Power	50 W
Temperature Range	-40/+120°C