



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--------------------|
| Series | PMR209 |
| Dielectric | Metallized Paper |
| Style | Radial |
| Features | RC Unit approved |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Qualifications | ENEC, UL, cUL |
| Construction | Molded |
| Typical Component Weight | 13.5 g |
| Miscellaneous | Resistor= 47 Ohms. |

Dimensions

| | |
|----|-----------------|
| L | 30.5mm MAX |
| H | 22mm MAX |
| T | 15.3mm MAX |
| S | 25.4mm +/-0.4mm |
| LL | 30mm +5mm |
| F | 1mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 75 |

Specifications

| | |
|-----------------------|-------------|
| Capacitance | 0.47 uF |
| Tolerance | 20% |
| Voltage DC | 630 VDC |
| Voltage AC | 250 VAC |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Insulation Resistance | 2.128 GOhms |
| Safety Class | X2 |