



Click [here](#) for the 3D model.

### Dimensions

L	23.6mm MAX
W	4mm MAX
T	1.9mm MAX

### Packaging Specifications

Typical Component Weight	1.2
Packaging	Bulk Tray, Box
Packaging Quantity	1000

### General Information

Style	Rubber Cased
Description	Multilayer Piezoelectric Bimorph Actuator
RoHS	With Exemptions
SCIP Number	96933f00-7dd0-4e6d-8a13-be939072857c
REACH	SVHC (PZT - CAS 12626-81-2)

### Specifications

Series	R11
Capacitance	1 uF
Capacitance Tolerance	20%
Maximum Driving Voltage	25 V Peak-Peak
Resonant Frequency	6 kHz
Temperature Range	-25/+70°C