



Click [here](#) for the 3D model.

### Dimensions

D	12mm MAX
L	15mm MAX
S	8.5mm NOM
F	0.55mm NOM

### Packaging Specifications

Typical Component Weight	5.86 g
Packaging	Bulk
Packaging Quantity	1600

### General Information

Series	SBC6
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Soft Lead Terminal

### Specifications

Inductance	100 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	No
Current	1.7 Amps
DC Resistance	0.13 Ohms