



Click [here](#) for the 3D model.

General Information

Series	SBCP-80HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Notes	Contains 4 Reels of 500 pieces each.

Specifications

Inductance	68 uH (0.01 MHz)
Inductance Tolerance	10%
Rated Current	1.7 Amps
Temperature Range	-20/+105°C
Shielded	No
DC Resistance	160 mOhms
DC Resistance	0.16 Ohms

Dimensions

D	9.5mm MAX
L	11mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Typical Component Weight	2.5 g
Packaging	Ammo
Packaging Quantity	2000