



Click [here](#) for the 3D model.

General Information

Series	SBCP-87HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Notes	Contains 4 Reels of 500 pieces each.

Dimensions

D	9.5mm MAX
L	8.5mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Typical Component Weight	1.6 g
Packaging	Ammo
Packaging Quantity	2000

Specifications

Inductance	220 uH (0.01 MHz)
Inductance Tolerance	10%
Inductance	220 uH
Temperature Range	-20/+105°C
Shielded	No
Current	0.65 Amps
DC Resistance	570 mOhms
DC Resistance	0.57 Ohms