


SBT-0180W

Aliases (UDLSBTW0180W00) Common Mode Chokes - Signal, KEMET, SBT-01W, Through-Hole, Common Mode, 80 uH, 35%



General Information	
Series	SBT-01W
Style	Through-Hole
RoHS	Yes
Miscellaneous	Inductance: 70mAmps (1kHz).

Click here for the 3D model.

Dimensions	
L	7.5mm MAX
W	6.4mm MAX
Н	8mm MAX
LL	4.5mm +/-1mm
S	5.08mm +/-0.5mm
S1	2.54mm +/-0.3mm
F	0.6mm NOM

Bulk, Box

500 mg

100

Packaging Specifications

Typical Component Weight

Packaging Quantity

Packaging

Specifications		
Voltage DC	50 VDC	
Inductance	80 uH	
Inductance Tolerance	35%	
Temperature Range	-25/+70°C	
DC Resistance	55 mOhms (MAX)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO