


SC-01-S07J

Aliases (UALSC01S07J000)

Common Mode Chokes - Power, KEMET, SC Three Phase, Through-Hole, Common Mode, 700 uH



General Information	
Series	SC Three Phase
Style	Through-Hole
Features	High Impedance
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 15 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	24.5mm MAX
Т	22mm MAX
Н	27.5mm MAX
LL	3.8mm +/-1mm
S	8mm NOM
S1	15mm NOM
Wire Size	0.5mm

Specifications	
Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	0.7 mH
Rated Current	1A
Temperature Range	-25/+120°C
DC Resistance	38 mOhms

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	200	
Typical Component Weight	16.1 g	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/26/2025 © 2006 - 2025 YAGEO