


SC-02-E115J

Aliases (UALSC02E115J00)

Common Mode Chokes - Power, KEMET, SC-J, Through-Hole, Common Mode, 0.0115 H



General Information	
Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	25mm MAX
Т	15.4mm MAX
Н	27.5mm MAX
LL	3.5mm +/-1mm
S	13mm NOM
S1	11mm NOM
Wire Size	0.5mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	400
Typical Component Weight	13 g

Specifications	
Voltage AC	250 VAC
Inductance	11.5 mH
Rated Current	2 A
Temperature Range	-40/+120°C
DC Resistance	155 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/19/2025 © 2006 - 2025 YAGEO