



Click [here](#) for the 3D model.

Dimensions	
D	35mm MAX
T	24mm MAX
H	34mm MAX
LL	4.5mm +/-1mm
S	18mm NOM
S1	16mm NOM
Wire Size	1.8mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	200
Typical Component Weight	39.4 g

General Information	
Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	0.3 mH (1 kHz)
Current	20 A
Temperature Range	-40/+120°C
DC Resistance	4 mOhms