



Click [here](#) for the 3D model.

### Dimensions

D	28mm MAX
T	18.4mm MAX
H	26.5mm +1/-0.6mm
LL	3.5mm +/-0.5mm
S	17mm +/-0.5mm
S1	12mm +/-0.5mm
Wire Size	1.9mm
BD	24.2mm +/-0.5mm
BT	17.85mm +/-0.5mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	210
Typical Component Weight	17.4 g

### General Information

Series	SC19XV
Style	Through-Hole
Features	High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Nanocrystal

### Specifications

Voltage AC	1000 VAC
Voltage DC	1000 VDC
Inductance	0.11 mH
Current	30 A
Temperature Range	-40/+150°C
DC Resistance	0.747 mOhms