


[Click here for the 3D model.](#)
General Information

Series	SCR22
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	65 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions

D	32mm MAX
T	24mm MAX
H	31mm MAX
LL	5mm +/-2mm
S	14mm NOM
S1	18mm NOM
Wire Size	1.3mm

Specifications

Voltage AC	250 VAC
Inductance	1500 uH
Rated Current	10 A
Temperature Range	-40/+120°C
DC Resistance	12 mOhms

Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	33 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.