



Click [here](#) for the 3D model.

### General Information

Series	SH
Style	Through-Hole
RoHS	Yes
Miscellaneous	For 3 Lines.

### Specifications

Voltage DC	50 VDC
Inductance	1.7 uH
Temperature Range	-25/+80°C
DC Resistance	81 mOhms (per Line MAX)

### Dimensions

L	9mm MAX
W	10mm MAX
H	10.5mm MAX
LL	3mm +/-0.7mm
S	6.5mm MAX

### Packaging Specifications

Typical Component Weight	1g
--------------------------	----