


SHO-402

Aliases (UDLSHO04020000, SHO402) Common Mode Chokes - Signal, KEMET, SHO, Through-Hole, Common Mode, 99 uH



General Information	
Series	SHO
Style	Through-Hole
RoHS	Yes

Click here for the 3D model.

Dimensions	
L	7.5mm MAX
T	5mm MAX
Н	7.5mm MAX
LL	4mm +/-2mm

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	6000
Typical Component Weight	370 mg

Specifications	
Voltage DC	50 VDC
Inductance	99 uH
Temperature Range	-25/+80°C
DC Resistance	120 mOhms (per Line MAX)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO