


SHO-501

Aliases (UDLSHO05010000, SHO501) Common Mode Chokes - Signal, KEMET, SHO, Through-Hole, Common Mode. 17.5 uH



General Information		
Series	SHO	
Style	Through-Hole	
RoHS	Yes	

Click here for the 3D model.

Dimensions	
L	6.2mm MAX
T	3.4mm MAX
Н	6.2mm MAX
LL	4mm +/-2mm

200 mg

Typical Component Weight

LL	4111111 +/ -2111111	DC Resistance
Packaging Specifications		
Packaging	Bulk, Box	
Packaging Quantity	6000	

Specifications	
Voltage DC	50 VDC
Inductance	17.5 uH
Temperature Range	-25/+80°C
DC Resistance	105 mOhms (per Line MAX)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO