



Click [here](#) for the 3D model.

General Information

Series	SN
Style	Through-Hole
Features	Compact Size
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Fe

Dimensions

D	28mm MAX
H	15mm MAX
LL	20mm +/-2mm
S	10mm
L2	2mm MAX
Wire Size	1mm

Packaging Specifications

Packaging	Bulk
Typical Component Weight	23.7 g

Specifications

Inductance	250 uH
Rated Current	5 A
Temperature Range	-40/+105°C
DC Resistance	0.06 mOhms