



General Information

| | |
|---------------|--|
| Series | SS11V/H-CH |
| Style | Through-Hole Bobbin |
| RoHS | Yes |
| Miscellaneous | Inductance Measurement Condition: 1kHz 1V KC530. |

Dimensions

| | |
|----|---------------|
| L | 22mm +/-1mm |
| T | 14.5mm +/-1mm |
| H | 21.5mm +/-1mm |
| LL | 3.5mm +/-1mm |
| S | 13mm +/-0.5mm |
| S1 | 10mm +/-0.5mm |
| F | 0.8mm NOM |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 35 mH |
| Rated Current | 400 mA |
| Temperature Range | -25/+120°C |
| DC Resistance | 2.6 Ohms |

Packaging Specifications

| | |
|--------------------------|--------|
| Typical Component Weight | 10.7 g |
|--------------------------|--------|