


## SS17VA-R10025

Aliases (UAL17VAR100250, SS17VA/HA-R10025)

Obsolete

Common Mode Chokes - Power, KEMET, SS17VA/HA, Through-Hole Bobbin, Common Mode, 2,500 uH



General Information	
Series	SS17VA/HA
Style	Through-Hole Bobbin
RoHS	Yes
Notes	recommended replacement part SSR10VS-10135.
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530 or equivalent.

Dimensions	
L	17mm +/-1mm
Т	12mm +/-1mm
Н	15.1mm +/-1mm
LL	3.5mm +/-1mm
S	12mm +/-1mm
S1	8mm +/-1mm
Wire Size	0.37mm
F	0.6mm +/-0.1mm

Specifications	
Voltage AC	250 VAC
Inductance	2.5 mH
Rated Current	1A
Temperature Range	-25/+120°C
DC Resistance	0.38 Ohms

Packaging Specification	ons
-------------------------	-----

Typical Component Weight 6 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/20/2025 © 2006 - 2025 YAGEO