



Click [here](#) for the 3D model.

Dimensions

L	31mm +/-1mm
T	22.5mm +/-1mm
H	33mm +/-1mm
S	19.5mm +/-0.5mm
S1	11mm +/-0.5mm
Wire Size	0.6mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	35.2 g

General Information

Series	SS30V
Style	Through-Hole
RoHS	Yes
Notes	Replacement For SS35V Type And SS28V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	14.5 mH
Current	1.8 A
Temperature Range	-40/+120°C
DC Resistance	0.23 Ohms