



General Information

Series	SU-10VD
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Ni-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	10 uH
Current	1 A
Temperature Range	-25/+120°C
DC Resistance	0.1 Ohms

Click [here](#) for the 3D model.

Dimensions

L	18mm MAX
T	16mm MAX
H	20mm MAX
LL	4mm MIN
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.45mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	700
Typical Component Weight	5.7 g